

HSN-GlueSB001

Description

HSN-GlueSB001 is a high-performance solvent-based adhesive specially formulated for industrial use. It offers fast drying, strong bonding strength, and excellent adhesion to various materials, including textiles, rubber, plastics, and metals.

Keterangan

HSN-GlueSB001 adalah lem berbasis solvent (solvent-based adhesive) berkekuatan tinggi, diformulasikan khusus untuk aplikasi industri. Produk ini cepat kering, memiliki daya rekat kuat, dan mampu menempel pada berbagai jenis permukaan, termasuk tekstil, karet, plastik, dan logam.

Technical Data

Appearance	: Yellowish Liquid
Base	: Polychloroprene
Density@20°C	: 0.830 g/ml
Viscosity	: Low
Solubility (water)	: Insoluble

Benefit

1. Used for bonding accessories, fabric reinforcement, and rubber or synthetic components in manufacturing or repair.
2. Solvent-based glue produces a durable and strong bond, even in extreme conditions such as high humidity and high temperatures.

Application

1. Ensure surfaces are clean, dry, and free from oil or dust.
2. Apply HSN-GlueSB001 evenly to both surfaces to be joined.
3. Firmly press the surfaces together.
4. Allow 12-24 hours for maximum bond strength.

Manfaat

1. Untuk pelapisan, pemasangan aksesoris, dan penyatuan bahan tekstil atau karet dalam proses produksi atau perbaikan.
2. Lem solvent-based menghasilkan ikatan yang tahan lama dan kuat, bahkan dalam kondisi ekstrem seperti kelembaban tinggi dan suhu tinggi.

Cara Penggunaan

1. Pastikan permukaan bersih, kering, dan bebas dari minyak atau debu.
2. Oleskan HSN-GlueSB001 secara merata pada kedua permukaan yang akan direkatkan.
3. Tekan kedua permukaan dengan kuat.
4. Biarkan selama 12-24 jam untuk kekuatan maksimal.

Health & Safety

- Avoid direct contact with skin and eyes.
- Wear appropriate PPE: organic vapor mask, gloves, and eye protection during application.

Storage

- Store in a cool, dry place in tightly sealed containers.
- Keep away from heat, direct sunlight, and open flame.

Shelf Life

12 months under proper sealed and cool storage conditions.

Packaging

- 1 Liter can
- 5 Liter can
- 20 Liter can
- Custom bulk packaging available upon request.

Kesehatan & Keamanan

- Hindari kontak langsung dengan kulit dan mata.
- Gunakan APD seperti masker organik, sarung tangan, dan pelindung mata saat aplikasi.

Penyimpanan

- Simpan di tempat sejuk dan kering, dalam wadah tertutup rapat.
- Jauhkan dari sinar matahari langsung, panas, dan api terbuka.

Masa Kadaluarsa

12 bulan dalam kondisi tertutup dan penyimpanan yang sesuai.

Kemasan

- Kaleng 1 Liter
- Kaleng 5 Liter
- Kaleng 20 Liter
- Kemasan kustom tersedia untuk volume besar.